


Model	HFS 6125SQ	HFS 6125SQY	HFS 6130SQ	HFS 6130SQY
Overall Diameter (mm)	12.50	12.50	13.00	13.00

Optic	6.00 mm		
Optic Design	Aberration Neutral, Negative Aspheric Biconvex		
Haptic Design	Step Vaulted "C" Design, 0 Angulation		
PCO Protection	360° Perfect Square edge around the optic edge		
Delivery system	Preloaded / Non preloaded		
Power Range	-10.00 D to +40.0 D (increments 0.50 D)		
Material	Hydrophobic, Refractive index : 1.4933+0.002		
A.Constant		Ultrasound	Optical Biometry
	SRK/T	118.4	118.7
	SRK/II	118.6	118.9

Specification: Glistening Free IOL



Scan to view loading procedure


OPTIMA JET **Preloaded Injector System** is specially designed for smoother and safer delivery of Hydrophobic IOL

OPTIMA JET **Non-Preloaded Injector System** is smoother and safer delivery of Hydrophobic IOL

OPTIMA JET injector system deliver the IOL from **1.80 mm to 2.60 mm Incision** with various cartridges

Click-lock mechanism thereby securing the lens in the exact position for a perfect lens delivery into the eye

Lens insertion is gentle and without the lens wedging or twisting ensure a controlled release, and consequently a precise positioning in the eye



Standard Aspheric optics vision performance under low light



Aberration neutral **Optima VUE** Hydrophobic aspheric Foldable excellent visual performance under low light

